



Model 425 Gaussmeter ✓RoHS



Model 425 features

- Field ranges from 350 mG to 350 kG
- DC measurement resolution to 4¼ digits (1 part of ±35,000)
- Basic DC accuracy of ±0.20%
- DC to 10 kHz AC frequency
- USB interface
- Large liquid crystal display
- Sort function (displays pass/fail message)
- Alarm with relay
- Standard and custom probes available
- CE mark certification





Introduction

Designed to meet the demanding needs of the permanent magnet industry, the Lake Shore Model 425 gaussmeter provides high-end functionality and performance in an affordable desktop instrument. Magnet testing and sorting have never been easier. When used in combination with the built-in relay and audible alarm features, the Model 425 takes the guesswork out of pass/fail criteria. Additional features including DC to 10 kHz AC frequency response, max hold and relative measurement make the Model 425 the ideal tool for your manufacturing, quality control and R&D flux density measurement applications. Put the Model 425 gaussmeter to use with confidence knowing it's supported by industry leading experts in magnet measurement instrument, sensor, and Hall probe technology.

Throughput

Throughput involves much more than just the update rate of an instrument. An intuitive menu navigation and keypad, along with overall ease of use are equally important. The Model 425 is designed with these qualities in mind. The operation is straightforward, with user display prompts to aid set-up. We understand that time is money! In addition to being user friendly, the automated magnet testing and sorting features of the Model 425 streamline sorting and testing operations. In addition, hot swapping of Hall probes allows

you to switch probe types without powering the instrument off and back on. These features support increased productivity, allowing you to spend less time setting up your instrument and more time working on the task at hand.

DC measurement mode

Static or slowly changing fields are measured in DC mode. In this mode, the Model 425 uses probe field compensation to correct for probe nonlinearities, resulting in a DC accuracy to $\pm 0.20\%$. Measurement resolution is enhanced with internal filtering, allowing resolution to $4\frac{3}{4}$ digits with reading rates to 30 readings per second over the USB interface.

AC measurement mode

In addition to the DC measurement mode, the Model 425 offers an AC measurement mode for measuring periodic AC fields. The instrument provides an overall frequency range of 10 Hz to 10 kHz and is equipped with both narrow and wide band frequency modes. While in narrow band mode, frequencies above 400 Hz are filtered out for improved measurement performance.

Measurement features

The Model 425 offers a variety of features to enhance the usability and convenience of the gaussmeter.

Autorange: In addition to manual range selection, the instrument automatically chooses an appropriate range for the measured field. Autorange works in DC and AC measurement modes.

Probe zero: Allows you to zero all ranges while in DC mode with the simple push of a key.

Display units: Field magnitude can be displayed in units of G, T, Oe, and A/m with resistance in Ω .

Max hold: The instrument stores and displays the captured maximum DC or AC field reading.

Relative reading: The relative mode calculates the difference between a live reading and the relative setpoint to highlight deviation from a known field point. This feature can be used in DC or AC measurement modes.

Instrument calibration: Lake Shore recommends an annual recalibration schedule for all precision gaussmeters. Recalibrations are always available from Lake Shore, but the Model 425 allows you to field calibrate the instrument if necessary. Recalibration requires a computer interface and precision low resistance standards of known value.



Instrument probe features

The Model 425 offers the best measurement performance when used along with Lake Shore Hall probes. Firmware-based features work in tandem with the probe's calibration and programming to ensure accurate, repeatable measurements and ease of setup. Many of the features require probe characteristics that are stored in the probe connector's non-volatile memory.

Probe field compensation: The Hall effect devices used in gaussmeter probes produce a near linear response in the presence of a magnetic field. The small nonlinearities present in each individual device can be measured and subtracted from the field reading. Model 425 probes are calibrated in a way to provide the most accurate DC readings.

Probe information: The gaussmeter reads the probe information on power up or any time the probe is changed to allow hot swapping of probes. Critical probe information can be viewed on the front panel and read over the computer interface to ensure proper system configuration.

Extension cable: The complex nature of Hall effect measurements makes it necessary to match extension cables to the probe when longer cables are needed. Keeping probes and their extensions from getting mixed up can become a problem when more than one probe is used. The Model 425 alleviates most of the hassle by allowing you to match probes to extension cables in the field. Stored information can be viewed on the front panel and read over the computer interface to ensure proper mating.

Hall effect generators (magnetic field sensors): The Model 425 will operate with a discrete Lake Shore Hall effect generator when a suitable probe is not available. You can program the nominal sensitivity and serial number into an optional HMCBL blank connector to provide all gaussmeter functions except field compensation. If no sensitivity information is available, the Model 425 reverts to resistance measurement.

Display and interface features

Keypad

The instrument keypad has 14 keys with individual keys assigned to frequently used features. Menus are reserved for less frequently used setup operations. The keypad can be locked out to prevent unintended changes of instrument setup.

Alarm, relay and sort

High and low alarm functions and one relay are included with the instrument, and can be used to automate repetitive magnet testing and sorting operations. Alarm actuators include display annunciator, audible beeper, and a relay. The alarm can be configured to display a pass or fail message and the relay can be configured to activate a mechanism to separate parts that meet pre-set fail criteria. The relay can also be controlled manually for other system needs.

Monitor output

The monitor output provides an analog representation of the reading that is corrected for probe offset and nominal sensitivity. This feature makes it possible to view the analog signal, which has not been digitally processed. The monitor output can be connected to an oscilloscope or data acquisition system.

Computer interface

The Model 425 is equipped with a universal serial bus (USB) interface. It emulates an RS-232C serial port at a fixed baud rate of 57,600, but with the physical connections of a USB. In addition to gathering data, nearly every function of the instrument can be controlled through the USB interface. The reading rate over the interface is nominally 30 readings per second. A LabVIEW™ driver is available from the downloads section of the Lake Shore website at www.lakeshore.com.

The Model 425 has a 2-line by 20-character liquid crystal display. During normal operation, the display is used to report field readings and give results of other features such as max or relative. When setting the instrument parameters, the display gives you meaningful prompts and feedback to simplify operation.

Display configuration examples

Normal reading—the default mode with the display of the live DC field reading.

Max DC hold on—the maximum value is shown in the lower display while the upper display contains the live DC field reading.

Alarm on—the alarm gives an audible and visual indication of when the field value is selectively outside or inside a user specified range. The relay can be associated with the alarm.

Sort on—the live reading is shown in the upper display while the lower display contains the pass/fail (repetitive sorting or testing) message. The relay facilitates pass/fail operation.



Model 425 specifications (Does not include probe error, unless otherwise specified)

General measurement

Input type: Single Hall effect sensor

Maximum update rate: 30 rdg/s

Probe features: Linearity compensation, probe zero, and hot swap

Measurement features: Autorange, max hold, relative mode, and filter

Probe connector: 15-pin D-sub

DC measurement

Probe type ranges	Filter on 4½-digit resolution	Filter off 3½-digit resolution
HST probe		
350 kG	000.01 kG	000.1 kG
35 kG	00.001 kG	00.01 kG
3.5 kG	0.0001 kG	0.001 kG
350 G	000.02 G	000.1 G
HSE probe		
35 kG	00.001 kG	00.01 kG
3.5 kG	0.0001 kG	0.001 kG
350 G	000.01 G	000.1 G
35 G	00.001 G	00.01 G
UHS probe (discontinued)		
35 G	00.001 G	00.01 G
3.5 G	0.0001 G	0.001 G
350 mG	000.02 mG	000.1 mG

Measurement resolution (RMS noise floor): Indicated by value in above table for shorted input

Display resolution: Indicated by number of digits in above table

DC accuracy: $\pm 0.20\%$ of reading $\pm 0.05\%$ of range

DC temperature coefficient: -0.01% of reading -0.003% of range/ $^{\circ}\text{C}$

DC filter: 16-point moving average

AC measurement

Probe type ranges	3½-digit resolution
HST probe	
350 kG	000.1 kG
35 kG	00.01 kG
3.5 kG	0.001 kG
350 G	000.1 G
HSE probe	
35 kG	00.01 kG
3.5 kG	0.001 kG
350 G	000.1 G
35 G	00.01 G
UHS probe (discontinued)	
35 G	00.01 G
3.5 G	0.001 G
350 mG	000.1 mG

Measurement resolution (RMS noise floor): Indicated by value in above table, measured at mid-scale range

Display resolution: Indicated by number of digits in above table

	Narrow band mode	Wide band mode
AC accuracy	$\pm 2\%$ of rdg, $\pm 0.05\%$ of rng (20 to 100 Hz); $\pm 2.5\%$ of rdg, $\pm 0.05\%$ of rng (10 to 400 Hz)	$\pm 2\%$ of rdg, $\pm 0.05\%$ of rng (50 Hz to 10 kHz)
AC frequency response	10 Hz to 400 Hz	50 Hz to 10 kHz
Minimum input signal	$> 1\%$ of rng	$> 1\%$ of rng, except $> 2\%$ of rng on lowest rng

AC specifications based on sine wave inputs or signals with crest factors < 4 .

AC temperature coefficient: $\pm 0.01\%$ of reading $\pm 0.006\%$ of range/ $^{\circ}\text{C}$

Front panel

Display: 2-line \times 20-character LCD display module with 5.5 mm high characters and LED backlight

Display units: Gauss (G), tesla (T), oersted (Oe), and ampere per meter (A/m)

Display update rate: 3 rdg/s

Display resolution: To $\pm 4\frac{3}{4}$ digits

Units multipliers: μ , m, k, M

Display annunciations: DC — DC measurement mode; RMS — AC RMS measurement mode; MAX — Max hold value; Δ — Alarm on

Keypad: 14-key membrane

Front panel features: Display contrast control and keypad lock-out

Interfaces

USB

Function: Emulates a standard RS-232 serial port

Baud rate: 57,600

Connector: B-type USB connector

Reading rate: To 30 rdg/s

Software support: LabVIEW™ driver (consult Lake Shore for availability)

Alarm

Settings: High setpoint, low setpoint, deadband, inside or outside, algebraic or magnitude, audible on/off, and sort

Actuators: Display annunciator, sort message, beeper, and relay

Relays

Number: 1

Contacts: Normally open (NO), normally closed (NC), and common (C)

Contact rating: 30 VDC at 2 A

Operation: Follows alarm or operated manually

Connector: Shared 25-pin D-sub

Monitor output

Configuration: Real time analog voltage output proportional to measured field

Range: ± 3.5 V

Scale: ± 3.5 V = \pm full scale on selected range

Frequency response: DC to 10 kHz

Accuracy: Offset and single point gain corrected to $\pm 0.5\%$ of reading $\pm 0.1\%$ of range, linearity is probe dependent

Minimum load resistance: 1 k Ω (short circuit protected)

Connector: Shared 25-pin D-sub

General

The Model 425 is the replacement for the Model 421 with a new software command set.

Ambient temperature: 15 $^{\circ}\text{C}$ to 35 $^{\circ}\text{C}$ at rated accuracy, 5 $^{\circ}\text{C}$ to 40 $^{\circ}\text{C}$ with reduced accuracy

Power requirement: 100 VAC to 240 VAC, 50 Hz to 60 Hz, 40 VA

Size: 216 mm W \times 89 mm H \times 318 mm D (8.5 in \times 3.5 in \times 12.5 in), half rack

Weight: 2.1 kg (4.6 lb)

Approvals: CE mark, RoHS

Probes and extensions

Probe compatibility: Full line of probes available—see page 27 for recommended stock probes available.

Hall sensor compatibility: Front panel programmable sensitivity and serial number for user supplied Hall sensor using HMCBL cable

Extension cable compatibility: Calibrated or uncalibrated probe extension cables with an EEPROM are available from 10 ft to 100 ft

Model 425 rear panel

- 1 Line input assembly
- 2 USB
- 3 Auxiliary I/O
- 4 Probe input



Stock probes  RoHS

The most commonly ordered probes for this gaussmeter. Others available starting on page 30.

Model	Orientation	Frequency range	Full-scale field ranges	Stem material	Stem length (in)	Probe part number
Model 425	Axial	DC to 400 Hz	HST-4: 35 G, 350 G, 3.5 kG, 35 kG	Aluminum	4	HMMA-2504-VF
		DC to 800 Hz	HST-4: 35 G, 350 G, 3.5 kG, 35 kG	Fiberglass	4	HMNA-1904-VF
		DC to 10 kHz	HSE: 3.5 G, 35 G, 350 G, 3.5 kG, 35 kG	Aluminum	4	HMMA-2504-VR
		DC to 20 kHz	HSE: 3.5 G, 35 G, 350 G, 3.5 kG, 35 kG	Fiberglass	4	HMNA-1904-VR
	Transverse	DC to 400 Hz	HST-4: 35 G, 350 G, 3.5 kG, 35 kG	Aluminum	4	HMMT-6J04-VF
		DC to 800 Hz	HST-4: 35 G, 350 G, 3.5 kG, 35 kG	Fiberglass	4	HMNT-4E04-VF
			HSE: 3.5 G, 35 G, 350 G, 3.5 kG, 35 kG	Aluminum	4	HMMT-6J04-VR
		DC to 20 kHz	HSE: 3.5 G, 35 G, 350 G, 3.5 kG, 35 kG	Fiberglass	4	HMNT-4E04-VR

Ordering information

Part number	Description
425	Model 425 gaussmeter

Please indicate your power/cord configuration:

1	100 V—U.S. cord (NEMA 5-15)
2	120 V—U.S. cord (NEMA 5-15)
3	220 V—Euro cord (CEE 717)
4	240 V—Euro cord (CEE 717)
5	240 V—U.K. cord (BS 1363)
6	240 V—Swiss cord (SEV 1011)
7	220 V—China cord (GB 1002)

Accessories included

G-106-253	I/O mating connector
G-106-264	I/O mating connector shell
4060	Small zero gauss chamber
119-053	Model 425 user manual

Accessories available

4065	Large zero gauss chamber
HMCBL-6	User programmable cable with EEPROM (6 ft)
HMCBL-20	User programmable cable with EEPROM (20 ft)
HMPEC-10-U	Probe extension cable with EEPROM (10 ft), uncalibrated
HMPEC-25-U	Probe extension cable with EEPROM (25 ft), uncalibrated
HMPEC-50-U	Probe extension cable with EEPROM (50 ft), uncalibrated
HMPEC-100-U	Probe extension cable with EEPROM (100 ft), uncalibrated
RM-1/2	Rack mount kit for one ½-rack gaussmeter in 483 mm (19 in) rack
RM-2	Rack mount kit for two ½-rack gaussmeter in 483 mm (19 in) rack

Calibration service

CAL-NEW-DATA	New instrument calibration with certificate and data
CAL-425-CERT	Instrument recalibration with certificate
CAL-425-DATA	Instrument recalibration with certificate and data

All specifications are subject to change without notice
Other probes available — see page 30

